

ALPHA STAINLESS

8478UAO125P62 BURDEOS

EAN 4031582313291



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	155 mm
Overall weight	0.67 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Stainless	✓

FITTING

Fitting type	Rectangular plate
Plate length	100 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Maximum)	60 mm
Plate hole diameter	9 mm

ALPHA STAINLESS

8478UAO125P62 BURDEOS

EAN 4031582313291



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

