

PRODUCT INFORMATION

DURATECH HEAT

BOG 100x35 HL45,5 asm.

EAN 4031582347227



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	551.16 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall weight	0.66 lb

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Black
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.31 in
Hub length	1.79 in
Body width	1.38 in
Hardness of tread (D)	90 Shore D

DURATECH HEAT

BOG 100x35 HL45,5 asm.

EAN 4031582347227

Order number 00035370

Product Drawings



BETTER MOBILITY. BETTER LIFE.

