PRODUCT INFORMATION

# DURATECH HEAT

## BOG 100x35 HL45,5 asm.

EAN 4031582347227



Image may differ from the original product

### WHEEL

| | |
|---|---|
| Body material | Plastic thermoset, heat-resistant |
| Tread material | Identical with wheel body |
| Bearing | Dry bearing bush |
| Wheel color | Black |
| Diameter | 3.94 in |
| Tread width | 1.38 in |
| Axle hole diameter | 0.31 in |
| Hub length | 1.79 in |
| Body width | 1.38 in |
| Hardness of tread (D) | 90 Shore D |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●○○○ |
| Attrition | ●●●●● |
| Corrosion resistance | ●●●●● |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Duratech heat |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 275.58 lb |
| Electric conductive | no |
| Stainless | Yes |
| Load capacity Static | 551.16 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 536 °F |
| Overall weight | 0.66 lb |

© Copyright 2026 TENTE International GmbH


# DURATECH HEAT

BOG 100x35 HL45,5 asm.

EAN 4031582347227

Order number 00035370

**Product Drawings**




© Copyright 2026 TENTE International GmbH