

DURATECH

TOP 080X70-Ø20 HL76

EAN 4031582322576
Order number 00804172



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	80 mm
Tread width	70 mm
Axle hole diameter	20 mm
Hub length	76 mm
Body width	70 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	700 kg
Load capacity at 6 km/h	560 kg
Load capacity Static	1400 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.446 kg

DURATECH

TOP 080X70-Ø20 HL76

EAN 4031582322576
Order number 00804172



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

