

SUPRATECH

PJR100X32-Ø12 HL44,4

EAN 4031582419306



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

| | |
|------------------------|---------------------|
| Materijal za telo | polipropilen |
| materijal omotaca | Termoplastična guma |
| Nošenje | kotrljajući lezaj |
| štitnici omotaca | Bez stražara |
| Prečnik | 100 mm |
| Širina omotac | 32 mm |
| dimenzija rupa osovina | 12 mm |
| dužina glavcine | 44,4 mm |

PERFORMANSE

| | |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ○ ○ |
| Buka u pokretu | ● ● ● ○ ○ |
| Ishrana | ● ● ● ○ ○ |
| otpornost na rdju | ● ● ● ○ ○ |

OSNOVNI ATRIBUTI

| | |
|--------------------------------|---------------------------|
| Naziv proizvoda | Supratech |
| Tip | Tocak |
| Standard | EN12530 - Kastori uređaja |
| Nosivost na 3 km/h | 80 kg |
| Statički Nosivost | 160 kg |
| Temperaturni opseg (Minimalno) | -20 °C |
| Opseg temperature (maksimalni) | 60 °C |
| Ukupna težina | 0,136 kg |

SUPRATECH

PJR100X32-Ø12 HL44,4

EAN 4031582419306



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

