PRODUCT INFORMATION

# GALEA

5075PJP125R05-28x40

EAN 4031582379464



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●○ |
| Movement Noise | ●●●●○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Galea |
| Type | Swivel castor with wheel brake |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 162 mm |
| Overall width | 66 mm |
| Overall weight | 0.77 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Closed |
| Swivel Bearing | Two ball races |
| Offset | 40 mm |
| Swivel radius | 129 mm |
| Swivel interference | 258 mm |
| Dome diameter | 59 mm |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 125 mm |
| Tread width | 30 mm |
| Hardness of tread (A) | 87 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Solid stem, round |
| Bolt diameter | 28 mm |
| Bolt length | 40 mm |

© Copyright 2026 TENTE International GmbH


# GALEA


5075PJP125R05-28x40

EAN 4031582379464

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



© Copyright 2026 TENTE International GmbH