PRODUCT INFORMATION

# AGILA TWIN

2975DIK050P40

EAN 4031582302790



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Agila twin |
| Type | Swivel castor with wheel brake |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 60 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 120 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 85 °C |
| Overall Height | 69 mm |
| Overall width | 57 mm |
| Overall weight | 0.4 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 25 mm |
| Swivel radius | 77 mm |
| Swivel interference | 155 mm |
| Dome diameter | 53 mm |

## WHEEL

| | |
|---|---|
| Body material | Sheet Steel |
| Tread Material Mix | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Wheel Color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 50 mm |
| Tread width | 19 mm |
| Body width | 19 mm |
| Hardness of tread (A) | 80 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Square plate |
| Plate length | 60 mm |
| Plate width | 60 mm |
| Plate hole length (Minimum) | 38 mm |
| Plate hole length (Maximum) | 48 mm |
| Plate hole width (Minimum) | 38 mm |
| Plate hole width (Maximum) | 48 mm |
| Plate hole diameter | 6.3 mm |

© Copyright 2026 TENTE International GmbH


# AGILA TWIN


2975DIK050P40


EAN 4031582302790

Order number 00031165

**Product Drawings**






© Copyright 2026 TENTE International GmbH