

MAXTECH

PAP4X1.25-Ø9.8 HL41

EAN 4031582436181



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 101.6 mm |
| Tread width | 31.75 mm |
| Axle hole diameter | 9.8 mm |
| Hub length | 41 mm |
| Hardness of tread (D) | 41 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ○ ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-------------------------|--|
| Product name | Maxtech |
| Housing type | Wheel |
| Standard | Institute of Casters and Wheel Manufacturers |
| Load capacity at 3 km/h | 125 kg |
| Load capacity Static | 250 kg |

MAXTECH

PAP4X1.25-Ø9.8 HL41

EAN 4031582436181



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

