

NOVATECH

ITP 150x50-Ø20 HL60

EAN 4031582319897



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE


Roll Performance	● ● ● ● ● ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1433 lb
Load capacity at 3.7 mph	1146.4 lb
Electric conductive	no
Stainless	no
Load capacity Static	2866.01 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	2.59 lb

WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	5.91 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D




PRODUCT INFORMATION

NOVATECH

ITP 150x50-020 HL60

EAN 4031582319997

Order number 00829121



BETTER MOBILITY. BETTER LIFE.