

MAXTECH

UAR100x36H45

EAN 4031582426953



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	440.92 lb
Electric conductive	no
Stainless	no
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	-7312 °F
Overall weight	0.73 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Diameter	3.94 in
Tread width	1.42 in
Axle hole diameter	0.47 in
Hub length	1.77 in
Bearing type	Roller Bea

FITTING

Bolt diameter	0.31 in
Bolt length	2.56 in