

ZETA REVERSE

468BTOO125P63 180°

EAN 4031582398205



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ● ○
Buka u pokretu	● ○ ○ ○ ○ ○
Ishrana	● ● ● ● ● ●
otpornost na rdju	● ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Zeta reverse
Tip	Okreni Tocak sa potpuna kocnica i usmerena kocnica napunjenom oprugom
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	700 kg
Nosivost na 6 km/h	560 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	164 mm
Ukupna težina	2.85 kg

KUCISTE

Materijal kućišta	Čelični list, veoma težak
oblik viljusk	siroko, Ojacano
okretni lezaj	Dve trke za loptu, Ojacano ili nerdjajuci
Boja	plavo cinkovano
ofset	60 mm
Otpor okretanju	360 mm

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	50 mm
Teškoća gazećeg omotac (D)	75 Šor D

PRILAGOĐAVANJE

Tip uklapanja	Pravougaona ploča
Dužina ploče	137 mm
Širina ploče	105 mm
Dužina otvora ploče (maksimalna)	105 mm
Širina otvora ploče (Minimalno)	75 mm
Širina otvora ploče (maksimalna)	80 mm
Prečnik otvora ploče	11 mm

ZETA REVERSE

468BTOO125P63 180°

EAN 4031582398205

Broj porudžbine 00860931
Product Drawings



BETTER MOBILITY. BETTER LIFE.

