

AGILA

2470UOO075P30-11 TFR

EAN 4031582390100



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	3.94 in
Overall weight	0.45 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.87 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	0.98 in
Swivel radius	2.46 in
Swivel interference	4.92 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in
Hint	Castors can be mounted with standard screws of any length.

AGILA

2470UOO075P30-11 TFR

EAN 4031582390100



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

