

NOVATECH

ITP100X40-Ø20 HL40

EAN 4031582437607



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	40 mm
Axle hole diameter	20 mm
Hub length	40 mm
Hardness of tread (A)	92 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.47 kg

NOVATECH

ITP100X40-Ø20 HL40

EAN 4031582437607



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

