

PRODUCT INFORMATION

NOVATECH

FTP 300x100-Ø40 HL120

EAN 4031582319439



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	11.81 in
Tread width	3.94 in
Axle hole diameter	1.57 in
Hub length	4.72 in
Body width	3.94 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	6878.41 lb
Load capacity at 3.7 mph	5732.01 lb
Electric conductive	no
Stainless	no
Load capacity Static	11464.02 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	41.47 lb




PRODUCT INFORMATION

NOVATECH

FTP 300x100-Ø40 HL120

EAN 4031582319439

Order number 10801175



BETTER MOBILITY. BETTER LIFE.