

# MONO

5025PJH080L51-10 RAL7035 REGULAR BRAKE

EAN 4031582460599



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

## CORE ATTRIBUTES

Product name	Mono
Housing type	Swivel castor with wheel brake
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Overall height	104 mm
Overall weight	0 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	80 mm
Tread width	24 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Offset	34 mm
Swivel interference	148 mm

# MONO

5025PJH080L51-10 RAL7035 REGULAR BRAKE

EAN 4031582460599



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

