

# MAXTECH

UAR 125x38-Ø12

EAN 4031582323160



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread Material Mix    | Polyurethane, injected |
| Bearing               | Roller bearing         |
| Wheel Color           | Blue grey (RAL7031)    |
| Threadguards          | Without threadguard    |
| Diameter              | 125 mm                 |
| Tread width           | 38 mm                  |
| Axle Hole Diameter    | 12 mm                  |
| Hub Length            | 44.4 mm                |
| Body width            | 38 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Maxtech                       |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 300 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 600 kg                        |
| Temperature range (Minimum) | -25 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall weight              | 0.32 kg                       |

# MAXTECH

UAR 125x38-Ø12

EAN 4031582323160

Order number 00030960  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

