

PRODUCT INFORMATION

BASETECH

POO100x36-Ø12 white

EAN 4031582410358



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Basetech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 352.74 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 705.48 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 0.23 lb                       |



BETTER MOBILITY. BETTER LIFE.

WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Identical with wheel body |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 3.94 in                   |
| Tread width           | 1.42 in                   |
| Axle hole diameter    | 0.47 in                   |
| Hub length            | 1.75 in                   |
| Hardness of tread (D) | 65 Shore D                |

# BASETECH

POO100x36-Ø12 white

EAN 4031582410358



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

