PRODUCT INFORMATION

BASETECH

POO100x36-Ø12 white

EAN 4031582410358

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Electric conductive	no
Stainless	no
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.23 lb

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.42 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Hardness of tread (D)	65 Shore D

© Copyright 2026 TENTE International GmbH


BASETECH

POO100x36-Ø12 white

EAN 4031582410358

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH