

PURETECH

DVR200X50-Ø20 HL58

EAN 4031582442465



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	205 kg
Load capacity Static	410 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	1.799 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (A)	85 Shore A

PURETECH

DVR200X50-Ø20 HL58

EAN 4031582442465



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

