

STEM

R10-8x28 / 8

EAN 4031582321487



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Threaded stem
Stem diameter	0.31 in

PERFORMANCE

Corrosion resistance	● ● ● ○ ○
----------------------	-----------

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Overall height	0.14 in
Overall weight	0.05 lb