

# ZETA

4681ICP200P63-92A

EAN 4031582478099



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product Name                | Zeta                                |
| Type                        | Swivel castor with directional lock |
| Standard                    | EN12533 - Heavy Duty Castors        |
| Load capacity at 4 km/h     | 800 kg                              |
| Load capacity at 6 km/h     | 640 kg                              |
| Electric Conductive         | No                                  |
| Stainless                   | No                                  |
| Load capacity Static        | 1600 kg                             |
| Temperature range (Minimum) | -20 °C                              |
| Temperature range (Maximum) | 70 °C                               |
| Overall Height              | 240 mm                              |
| Overall weight              | 3.59 kg                             |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Housing Material    | Steel sheet, very heavy                 |
| Fork shape          | Broad, reinforced                       |
| Swivel Bearing      | Two ball races, reinforced or stainless |
| Housing Color       | Blue passivated                         |
| Offset              | 55 mm                                   |
| Swivel radius       | 155 mm                                  |
| Swivel interference | 310 mm                                  |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Aluminium                      |
| Tread Material Mix    | Ultratech Polyurethane, casted |
| Bearing               | Precision ball bearing         |
| Axle                  | Screwed with nut               |
| Threadguards          | Without threadguard            |
| Diameter              | 200 mm                         |
| Tread width           | 50 mm                          |
| Hardness of tread (A) | 92 Shore A                     |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 105 mm                   |
| Plate hole length (Maximum) | 105 mm                   |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 80 mm                    |
| Plate hole diameter         | 11 mm                    |

# ZETA

4681ICP200P63-92A

EAN 4031582478099



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

