

# ALPHA

3477PIO080P30-13

EAN 4031582305210  
Order number 00029514



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	108 mm
Overall weight	0.902 kg

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	80 mm
Tread width	35 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	44.5 mm
Swivel radius	121 mm
Swivel interference	242 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

# ALPHA

3477PIO080P30-13

EAN 4031582305210  
Order number 00029514



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

