

WHEEL

DRR 080x30-Ø12 HL44,4

EAN 4031582410808



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Wheel
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.21 kg

WHEEL

Body material	Sheet Steel
Tread Material Mix	Wound tread made of canvas and phenolic resin
Bearing	Roller bearing
Wheel Color	Blue passivated
Threadguards	Without threadguard
Diameter	80 mm
Tread width	30 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Body width	30 mm
Hardness of tread (A)	85 Shore A

WHEEL

DRR 080x30-Ø12 HL44,4

EAN 4031582410808

Order number 00900249

Product Drawings



BETTER MOBILITY. BETTER LIFE.

