

PRODUCT INFORMATION

MAXTECH

PNP 200x30-Ø8 HL44

EAN 4031582320626



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.4 kg

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread Material Mix	Polyurethane, foamed
Bearing	Precision ball bearing
Wheel Color	Black
Threadguards	With threadguard
Diameter	200 mm
Tread width	30 mm
Axle Hole Diameter	8 mm
Hub Length	44 mm
Body width	30 mm
Hardness of tread (A)	70 Shore A

