PRODUCT INFORMATION

# LUMINA

## AA25PJI050B10-11x20/8

EAN 4031582457797

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Lumina |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 40 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 58 mm |
| Overall width | 55 mm |
| Overall weight | 0.09 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Polypropylene |
| Fork shape | Twin wheel housing, closed |
| Swivel Bearing | Stem, swiveling |
| Swivel radius | 63 mm |
| Swivel interference | 126 mm |

### WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 50 mm |
| Tread width | 10 mm |
| Hardness of tread (A) | 87 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Stem with grip ring, with collar |
| Stem diameter | 11 mm |

© Copyright 2026 TENTE International GmbH


# LUMINA

AA25PJI050B10-11x20/8

EAN 4031582457797

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



© Copyright 2026 TENTE International GmbH