

## LINEA LIGHT

5920UOH065L51-10

EAN 4031582403978



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●●○

## OSNOVNI ATRIBUTI

Naziv proizvoda Linea light

Tip Okretanje Tocak

Standard EN12528 - tockovi za namestaj

Nosivost na 3 km/h 50 kg

Statički Nosivost 100 kg

Temperaturni opseg (Minimalno) -10 °C

Opseg temperature (maksimalni) 40 °C

Sveukupna visina 68 mm

Ukupna širina 46 mm

Ukupna težina 0,092 kg

## TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Sa threadguard
Prečnik	65 mm
Širina omotac	13,9 mm

## KUCISTE

Materijal	poliamid
oblik viljuska	kuciste za dva Tocak
okretni lezaj	stablo , okretanje
okretni radijus	56 mm
Otpor okretanju	112 mm
Prečnik kupole	23 mm

## PRILAGOĐAVANJE

Tip uklapanja	zatvorena rupa za postavljanje B10
dimenzija rupa sraf	10 mm

Deutscher  
dizajner  
ClubInterzum  
nagradaIF nagrada za  
Dizajn

# LINEA LIGHT

5920UOH065L51-10

EAN 4031582403978



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

