

# BASETECH

POR125X40-Ø12 HL48

EAN 4031582320817  
Order number 00030948



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.47 in
Hub length	1.89 in
Body width	1.57 in
Hardness of tread (D)	65 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	440.92 lb
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.46 lb

# BASETECH

POR125X40-Ø12 HL48

EAN 4031582320817  
Order number 00030948



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

