

PRODUCT INFORMATION

ELASTECH

IEP300x60-Ø30 TFR

EAN 4031582428483



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	300 mm
Tread width	60 mm
Axle Hole Diameter	30 mm
Hub Length	60 mm
Hardness of tread (A)	67 Shore A

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	3.87 kg




PRODUCT INFORMATION

ELASTECH

IEP300x60-Ø30 TFR

EAN 4031582428483



BETTER MOBILITY. BETTER LIFE.