

DURATECH

TOP 082X93-Ø20 HL95

EAN 4031582322651
Broj porudžbine 00804028

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	82 mm
Širina omotac	93 mm
dimenzija rupa osovina	20 mm
dužina glavcine	95 mm
Širina tela	93 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204ZV

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	900 kg
Nosivost na 6 km/h	720 kg
Statički Nosivost	1800 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,566 kg

DURATECH

TOP 082X93-Ø20 HL95

EAN 4031582322651
Broj porudžbine 00804028



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

