

ALPHA

3470PIO200P30-13

EAN 4031582303797



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	440.92 lb
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	9.25 in
Overall weight	5.9 lb

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Hardness of tread (A)	80 Shore A

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	2.17 in
Swivel radius	6.1 in
Swivel interference	12.2 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

ALPHA

3470PIO200P30-13

EAN 4031582303797



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

