

ALPHA STAINLESS

8470UFX125P30-11

EAN 4031582370126
Order number 00038473



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha stainless |
| Type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 330.69 lb |
| Stainless | ✓ |
| Load capacity Static | 661.39 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 6.1 in |
| Overall weight | 2.38 lb |

WHEEL

| | |
|-----------------------|---------------------------------------|
| Body material | Polyamide |
| | soft |
| Tread material | Elastic tire, non-marking, vulcanized |
| Bearing | Precision ball bearing, sealed |
| Axle | Screwed with nut |
| Threadguards | With threadguard |
| Diameter | 4.92 in |
| Tread width | 1.57 in |
| Hardness of tread (A) | 64 Shore A |

HOUSING

| | |
|---------------------|------------------------|
| Material | Stainless steel, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 1.57 in |
| Swivel radius | 4.04 in |
| Swivel interference | 8.07 in |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.43 in |

ALPHA STAINLESS

8470UFX125P30-11

EAN 4031582370126
Order number 00038473



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

