PRODUCT INFORMATION

# ALPHA

## 3477UAR125P62 natural/3004

EAN 4031582305760



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Alpha |
| Type | Swivel castor with total lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 200 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 400 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall Height | 155 mm |
| Overall width | 75 mm |
| Overall weight | 1.09 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, heavy |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 40 mm |
| Swivel radius | 123 mm |
| Swivel interference | 246 mm |
| Dome diameter | 75 mm |

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Roller bearing |
| Axle | Screwed with nut |
| Wheel Color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

### FITTING

| | |
|---|---|
| Fitting type | Small rectangular plate |
| Plate length | 105 mm |
| Plate width | 80 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 60 mm |
| Plate hole width (Minimum) | 77 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 9 mm |

© Copyright 2026 TENTE International GmbH

# ALPHA

## 3477UAR125P62 natural/3004

EAN 4031582305760

Order number 00039100

**Product Drawings**

