

PRODUCT INFORMATION

PURETECH

FVP 250X80-Ø25 HL90

EAN 4031582319521
Order number 00801212



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Cast iron
Tread material	Solid rubber, black
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	250 mm
Tread width	80 mm
Axle hole diameter	25 mm
Hub length	90 mm
Body width	80 mm
Hardness of tread (A)	67 Shore A

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Puretech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	810 kg
Load capacity at 6 km/h	675 kg
Load capacity Static	1350 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	7.92 kg

PURETECH

FVP 250X80-Ø25 HL90

EAN 4031582319521
Order number 00801212



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

