

NOVATECH

FTP 140X54-Ø20 HL60

EAN 4031582346619
Broj porudžbine 00833009

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	140 mm
Širina omotac	54 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	54 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Pogodno za	jungheinrich_mic

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	840 kg
Nosivost na 6 km/h	700 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	3,04 kg

NOVATECH

FTP 140X54-Ø20 HL60

EAN 4031582346619

Broj porudžbine 00833009



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

