

# DURATECH

UOD125X40-Ø12 LM44,4 TFR

EAN 4031582485325



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing, stainless
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	12 mm
Hub length	44 mm
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.57 kg

# DURATECH

UOD125X40-Ø12 LM44,4 TFR

EAN 4031582485325



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

