

PRODUCT INFORMATION

NOVATECH

FTP 150x60-Ø25 HL60

EAN 4031582329520



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES


Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2116.44 lb
Load capacity at 3.7 mph	1763.7 lb
Electric conductive	no
Stainless	no
Load capacity Static	3527.39 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	8.69 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	5.91 in
Tread width	2.36 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	2.36 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D




PRODUCT INFORMATION

NOVATECH

FTP 150x60-025 H160

EAN 4031582389520

Order number 10827815



BETTER MOBILITY. BETTER LIFE.