

# PURETECH

PVR125x37-Ø12 HL48

EAN 4031582321272



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Puretech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 220.46 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 1.04 lb                       |

## WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Polypropylene       |
| Tread material        | Solid rubber, black |
| Bearing               | Roller bearing      |
| Threadguards          | Without threadguard |
| Diameter              | 4.92 in             |
| Tread width           | 1.46 in             |
| Axle hole diameter    | 0.47 in             |
| Hub length            | 1.89 in             |
| Hardness of tread (A) | 85 Shore A          |

# PURETECH

PVR125x37-Ø12 HL48

EAN 4031582321272

Order number 00030957

Product Drawings



BETTER MOBILITY. BETTER LIFE.

