

DURATECH

UOP200X50-Ø20

EAN 4031582323528
Order number 00002304



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 7.87 in |
| Tread width | 1.97 in |
| Axle hole diameter | 0.79 in |
| Hub length | 2.36 in |
| Hardness of tread (D) | 75 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Duratech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 1763.7 lb |
| Load capacity Static | 3527.39 lb |
| Temperature range (Minimum) | -13 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 2.22 lb |

DURATECH

UOP200X50-Ø20

EAN 4031582323528
Order number 00002304



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

