

# ELASTECH

SEP 160X50-Ø20 HL60 PLUS

EAN 4031582346664  
Order number 00834683



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Sheet steel, heavy
	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	68 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1190.49 lb
Load capacity at 3.7 mph	992.08 lb
Load capacity Static	1984.16 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	2.48 lb

# ELASTECH

SEP 160X50-Ø20 HL60 PLUS

EAN 4031582346664  
Order number 00834683



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

