

ALPHA STAINLESS

8470UOD080P30-11

EAN 4031582377149



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●○○○

Ishrana ●●●●●

otpornost na rdju ●●●●●

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	150 kg
nerdjajuci	✓
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	108 mm
Ukupna težina	0,663 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	kotrljajuci lezaj, nerdjajuci
osovina	Završena sa navrtkom
Prečnik	80 mm
Širina omotac	34 mm
Teškoća gazećeg omotac (D)	75 Šor D

KUCISTE

Materijal	nerdjajuci čelik, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	44,5 mm
okretni radijus	84,5 mm
Otpor okretanju	169 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm

ALPHA STAINLESS

8470UOD080P30-11

EAN 4031582377149



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

8470UOD080P30- ϕ 11

