

DURATECH

TOP125X50-Ø25 TFR

EAN 4031582478792



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide, heavy |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 50 mm |
| Axle hole diameter | 25 mm |
| Hub length | 60 mm |
| Hardness of tread (D) | 75 Shore D |
| Bearing type | 6204 |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Duratech |
| Type | Wheel |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 700 kg |
| Load capacity Static | 1400 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.805 kg |