

PRODUCT INFORMATION

NOVATECH

FTP200x75-Ø25 HL75

EAN 4031582428827



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES


|                             |          |
|-----------------------------|----------|
| Product Name                | Novatech |
| Type                        | Wheel    |
| Electric Conductive         | No       |
| Stainless                   | No       |
| Temperature range (Minimum) | -20 °C   |
| Temperature range (Maximum) | 60 °C    |
| Overall weight              | 7.99 kg  |



BETTER MOBILITY. BETTER LIFE.

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Cast iron              |
| Tread Material Mix    | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 200 mm                 |
| Tread width           | 75 mm                  |
| Axle Hole Diameter    | 25 mm                  |
| Hub Length            | 75 mm                  |
| Hardness of tread (A) | 92 Shore A             |




PRODUCT INFORMATION

**NOVATECH**

FTP200x75-Ø25 H175

EAN 4031582488277



BETTER MOBILITY. BETTER LIFE.