

# NOVATECH

RK.ETP078X78-Ø47X16

EAN 4031582330069  
Order number 00832672



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

## WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	78 mm
Tread width	78 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Ball bearing diameter	47 mm
Ball bearing width	16 mm

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	700 kg
Load capacity at 6 km/h	840 kg
Load capacity Static	1400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.674 kg

## TECHNICAL DRAWINGS

