

## S70-10X10 / 8

EAN 4031582321869



Image may differ from the original product

### PERFORMANCE

Corrosion resistance ● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Overall height	0.24 in
Overall weight	0.04 lb

### FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.39 in