

PRODUCT INFORMATION

ELASTECH HEAT

IDC 100x35-Ø8,3 HL45 tread-1023 INOX

EAN 4031582348620



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ○ ○ ○
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Elastech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	80 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall weight	0.57 kg

WHEEL

Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Damping, heat resistant
Bearing	Precision ball bearing, stainless
Wheel Color	Metallic
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle Hole Diameter	8.3 mm
Hub Length	45 mm
Body width	35 mm
Hardness of tread (A)	75 Shore A

ELASTECH HEAT

IDC 100x35-Ø8,3 HL45 tread-1023 INOX

EAN 4031582348620



BETTER MOBILITY. BETTER LIFE.

Product Drawings

