

ALPHA STAINLESS

8470UAO160P63 BURDEOS

EAN 4031582441819



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	771.62 lb
Load capacity Static	1543.23 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	7.87 in
Overall weight	2.04 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.57 in
Hardness of tread (D)	40 Shore D

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	2.17 in
Swivel radius	5.31 in
Swivel interference	10.63 in
Stainless	✓

FITTING

Fitting type	Rectangular plate
Plate length	4.13 in
Plate width	3.15 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

ALPHA STAINLESS

8470UAO160P63 BURDEOS

EAN 4031582441819



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

B470U00125P62-neu

