

# ALPHA STAINLESS

8478WOO125P63 BLANCA

EAN 4031582446593



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●●
Corrosion resistance	●●●●●

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	507.06 lb
Stainless	✓
Load capacity Static	1014.13 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	356 °F
Overall height	6.34 in
Overall weight	3.15 lb

## WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.57 in
Hardness of tread (D)	75 Shore D

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

# ALPHA STAINLESS

8478WOO125P63 BLANCA

EAN 4031582446593



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

