

# FOOTMASTER

## FOOT MASTER GASD-100-ASF-HUD

EAN 4031582495218  
Order number 00800106



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

### HOUSING

Offset	32 mm
Swivel radius	90 mm
Swivel interference	180 mm
Dome diameter	112 mm

### FITTING

Plate length	112 mm
Plate width	112 mm
Plate hole length (Maximum)	92 mm
Plate hole width (Maximum)	92 mm
Plate hole diameter	9 mm

### PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

### CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	310 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall height	150 mm
Overall width	128 mm
Overall weight	8.45 kg

### WHEEL

Bearing	Unmachined hub
Diameter	100 mm
Tread width	30 mm
Body width	30 mm

# FOOTMASTER

FOOT MASTER GASD-100-ASF-HUD

EAN 4031582495218  
Order number 00800106



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

