

# FOOTMASTER

FOOT MASTER GATD-150-ASF-HUD

EAN 4031582495256



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ○ ○ ○ ○ ○ |
| Movement Noise       | ○ ○ ○ ○ ○ |
| Attrition            | ○ ○ ○ ○ ○ |
| Corrosion Resistance | ○ ○ ○ ○ ○ |

## CORE ATTRIBUTES

|                             |               |
|-----------------------------|---------------|
| Product Name                | Footmaster    |
| Type                        | Swivel castor |
| Load capacity at 3 km/h     | 630 kg        |
| Electric Conductive         | No            |
| Stainless                   | No            |
| Temperature range (Minimum) | -10 °C        |
| Temperature range (Maximum) | 90 °C         |
| Overall Height              | 200 mm        |
| Overall width               | 155 mm        |
| Overall weight              | 14.68 kg      |

## HOUSING

|                     |        |
|---------------------|--------|
| Offset              | 35 mm  |
| Swivel radius       | 123 mm |
| Swivel interference | 246 mm |
| Dome diameter       | 130 mm |

## WHEEL

|             |                |
|-------------|----------------|
| Bearing     | Unmachined hub |
| Diameter    | 150 mm         |
| Tread width | 40 mm          |
| Body width  | 40 mm          |

## FITTING

|                             |        |
|-----------------------------|--------|
| Plate length                | 145 mm |
| Plate width                 | 145 mm |
| Plate hole length (Maximum) | 120 mm |
| Plate hole width (Maximum)  | 120 mm |
| Plate hole diameter         | 11 mm  |

# FOOTMASTER

FOOT MASTER GATD-150-ASF-HUD

EAN 4031582495256

Order number 00800114

Product Drawings



BETTER MOBILITY. BETTER LIFE.

