

PRODUCT INFORMATION

DURATECH

MOP 250x50-Ø40 HL60

EAN 4031582320077



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	9259.4 lb
Load capacity at 3.7 mph	7716.17 lb
Electric conductive	no
Stainless	no
Load capacity Static	18518.81 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	8.58 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	1.97 in
Axle hole diameter	1.57 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6308

DURATECH


MOP 250x50-Ø40 HL60

EAN 4031582320077

Order number 00801034
Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

DURATECH

MOP 250x50-Ø40 HL60

EAN 4031582320077

Order number 00801634



BETTER MOBILITY. BETTER LIFE.